

# Top Supplies for Agilent 708-DS Dissolution Systems

Agilent technical experts have compiled a list of recommended supplies that you should consider using with your new instrument in order to keep your lab operational without any disruptions and to achieve optimal performance.

## Apparatus 1 – Rotating Basket



### Shafts

- **14-3613** Upper receptor shaft, 21 in. (total length when assembled)

### Basket shaft

- **14-3631** Basket shaft, lower interchangeable, 3-clip, USP

### Vessels

- **12-5149V** TruAlign vessel, 1L, clear  (Top Recommendation)
- **12-5149V** TruAlign vessel, 1L, clear, including certificate  (Top Recommendation)
- **12-1450** TruAlign vessel, 250 mL conversion kit, for Chinese Pharmacopeia (includes vessel, adapter, two-piece mini paddle, evaporation cover and manifold adapter), set of 6



### Thermal paper

- **G7910-87002** Thermal printer paper for use with 708-DS, 10 Shafts rolls/pk





### Cannulas

- **12-3222** Bent cannula with adjustable gauge 7.75 in. 708-DS




### Baskets

- **12-2100V** Basket, USP, 40-mesh  (Top Recommendation)
- **12-2100V** Basket, USP, 40-mesh with certificate  (Top Recommendation)



### Filters

- **17-4000** Full Flow Filter UHMWPE, blue, 10 µm, 100/pk
- **17-4005** Full Flow Filter UHMWPE, blue, 10 µm, 1000/pk  (Top Recommendation)





## Apparatus 2 – Rotating Paddle

### Shafts

- **14-3613** Upper receptor shaft, 21 in. (total length when assembled)



### Paddles

- **14-3603** lower interchangeable paddle, electropolished stainless steel, 1L  (Top Recommendation)
- **14-3609** lower interchangeable paddle, Diamond Like Carbon (DLC)-coated, 1L  (Top Recommendation)



### Vessels

- **12-5149V** TruAlign vessel, 1L, clear  (Top Recommendation)
- **12-5149V** TruAlign vessel, 1L, clear, including certificate  (Top Recommendation)
- **12-1450** TruAlign vessel, 250 mL conversion kit, for Chinese Pharmacopeia (includes vessel, adapter, two-piece mini paddle, evaporation cover, and manifold adapter), set of 6



### Thermal paper

- **G7910-87002** Thermal printer paper for use with 708-DS, 10 Shafts rolls/pk




### Cannulas

- **12-3222** Bent cannula with adjustable gauge 7.75 in. 708-DS



### Filters

- **17-4000** Full Flow Filter UHMWPE, blue, 10 µm, 100/pk
- **17-4005** Full Flow Filter UHMWPE, blue, 10 µm, 1000/pk  (Top Recommendation)



### Sinkers

- **12-3000** Capsule weight wire, 316 stainless steel, 0.032 in. dia., 50 ft.
- **12-3050** Capsule weight, 3-prong
- **12-3070** Sinker basket, Japanese Pharmacopoeia (JP)

